# **Technical Newsletter**

#tn12015-0008e



## Caution When Using Protective Films Other than HogoMax

### Please Do Not Use Products from Other Companies

Applying the water-soluble protective film "HogoMax" onto the processing surface prevents adhesion of debris (generated during laser processing).

DISCO laser equipment is specifically made for use with HogoMax. Use of products from other companies may result in the protective film not being applied properly onto uneven sections, causing debris adhesion to occur.


DISCO does not guarantee the use of any coating properties besides HogoMax. Customers will be charged for the optimization of coating conditions which are created through the use of products from other companies and repairs for equipment malfunctions caused through the use of said products, even if the equipment is still under warranty.

#### Applicable Equipment

DFL7161 / DFL7160 / DFL7020

#### Difference between HogoMax and Other Protective Films

Other protective films have a smaller processing margin, causing debris to form near the laser processing position, depending on the conditions.



Process condition : 5.9W\_40kHz\_Just focus
Wafer : mirror Si

#### For All Inquiries

For all inquiries relating to this matter, please contact your sales representative or our affiliate office.